FILTAIR SWX Series

Welding Safety



Quick Specs

Industrial Applications

Schools and training facilities Manufacturing and fabrication Fixed welding cells/stations

Processes

Stick (SMAW) Flux-cored (FCAW) MIG (GMAW) TIG (GTAW)

Filter Media

490 sq. ft. (45.52 sq. m)

Accu-Rated™ Airflow 875 cfm (413 L/sec.)

Sound Level at 5 ft. (1.5 m)

Standard: Approximately 75 dBA ZoneFlow™: Approximately 80 dBA

Extraction Arm 8 in. (203 mm) diameter

Telescoping: 3–4.5 ft. length **Standard:** 7, 10 or 12 ft. length **ZoneFlow**™: 10 or 12 ft. length

Wall- or column-mounted fume extraction systems designed specifically for welding.

Self-cleaning filter (SWX-S) model is available with choice of telescoping, standard or ZoneFlow extraction arm.

Disposable filter (SWX-D) model is available with choice of telescoping or standard extraction arm.

See page 11 for optional dual-arm add-on packages.

The capture zone redefined. Innovative, extended-capture fume extraction system designed specifically for welding.

Exclusive ZoneFlow™ technology creates a much larger capture area than existing source-capture products and minimizes arm interactions. See page 2 for more information.

Have a certified industrial hygienist test the air in your facility to determine equipment requirements and ensure adequate protection from contaminants.





Standard high-efficiency filter designed to capture weld fume



Exclusive ZoneFlow™ technology extends weld fume capture area



Filters air for welder and facility



Better protection, more welding



Fume extractor is warranted for one year, parts and labor.



Miller Electric Mfg. LLC

An ITW Welding Company 1635 West Spencer Street P.O. Box 1079 Appleton, WI 54912-1079 USA

Equipment Sales US and Canada

ZoneFlow technology.

Phone: 866-931-9730 FAX: 800-637-2315

International Phone: 920-735-4554 International FAX: 920-735-4125








ZoneFlow™ Technology

Extend your fume capture zone

Capturing fume at the source is critical to maintaining a clean breathing zone for the welder and keeping the facility clean.


ZoneFlow technology offers up to five feet of fume extraction versus up to 18 inches from conventional source capture extractors. By increasing the area of weld fume capture, it dramatically reduces the amount of interaction a welder has with an arm.




ZoneFlow tech talk

ZoneFlow technology creates a negative pressure zone that extends the weld particulate capture distance.

Air moving into the arm is still about 900 cfm. However, ZoneFlow technology also moves clean, filtered air out of the arm at approximately a 90-degree angle which creates a large negative pressure zone. This negative pressure zone forms a type of curtain that funnels the weld fume particulate towards the center of the arm, maximizing capture and extending the capture zone up to five feet deep and four feet wide.







Specifications (Subject to change without notice.)

| Filter Media | Accu-Rated™ Airflow | Extraction Arm Diameter | Sound Level | Motor | Power | Dimensions | Net Weight without Arm |
|------------------------------|-------------------------|----------------------------|---|-----------------------|--|---|--|
| 490 sq. ft. (45.52 sq. m) | 875 cfm (413 L/sec.) | 8 in. (203 mm) | Standard Approximately 75 dBA at 5 ft. (1.5 m) | 1 hp, 3,450 rpm | Blower motor 115 V, 1-phase, 60 Hz at approximately 11.9 A | H: SWX-D: 29 in. (737 mm) H: SWX-S: 33 in. (838 mm) W: 27.25 in. (692 mm) | Cabinet SWX-D: 130 lb. (59 kg) SWX-S: 195 lb. (88 kg) |
| | | | ZoneFlow™ Approximately 80 dBA at 5 ft. (1.5 m) | | ZoneFlow™ 115 V, 1-phase, 60 Hz at approximately 12 A | D: 33 in. (838 mm) | Blower/bracket 95 lb. (43 kg) |

System Benefits

SWX filter cabinet

Disposable and self-cleaning filter models available.

The disposable filter model works great for light duty and intermittent welding operations. Upgrade to self-cleaning models with high arc on time, extracting from heavy-fume processes, or when welding aluminum or galvanized materials. Self-cleaning models are also recommended for most dual-arm applications.



Self-cleaning model has additional features.

Designed to capture weld fume particles with a cleanable filter and safely deposit them in an integrated particle bin, the self-cleaning model provides unrivaled filtering performance.

One-minute cleaning cycle operates with a push of a button on the control panel.

Latches release a disposal drawer allowing it to slide out to provide easy and convenient access to empty out the collected particles.

Note: Compressed air required to operate cleaning mechanism.



Disposable filter (SWX-D) model



Self-cleaning filter (SWX-S) model

Fume extraction blower



Class leading suction power.

High-performance fan generates 1,200 cfm and creates an Accu-Rated minimum of 875 cfm extraction at the hood to better capture weld fumes and provide a cleaner environment.



Easy-to-operate extraction arms

Telescoping arms extend up to 4.5 feet and are ideal for smaller spaces.

Designed to fit small booth spaces used in training centers and educational booths. Telescopes from 3 to 4.5 feet with a wide range of motion to cover all positions.



Standard/ZoneFlow arms in multiple different sizes cover larger areas.

Designed to cover larger spaces, the standard arms are available in 7-, 10- and 12-foot versions and the ZoneFlow arms in 10- and 12-foot versions. External brackets and adjustments allow air to pass through with less resistance giving you stronger cfm (airflow).





Cleaner air with FilTek XL filters

The FilTek XL filter's higher MERV rating means unrivaled filtering performance.

Filters are rated on a MERV scale, which measures filter efficiency based on particle count. MERV ratings range from 1 to 16, with 16 being the best at filtering small particles — such as those found in weld fumes. The vast majority of weld fumes are less than one micron in diameter, or roughly 1/100th the width of a human hair.



Filters in common air filtration systems often have MERV ratings from 7 to 11. FilTek XL filters are rated at class-leading MERV 15–16 to capture up to 95 percent of weld fume particulates.

Filter media performance summary

FilTek XL filters have the highest efficiencies and lowest pressure drops to capture better, last longer, and lower operating costs.

MERV Comparison

| Applicable Weld Fume | Particle Size Range Efficiency %² | | | |
|---|-----------------------------------|-----------|------------|--|
| MERV Rating Categories¹ | 0.3 to 1 μm | 1 to 3 μm | 3 to 10 µm | |
| 10 | Not rated | 50-65% | 85% | |
| 11 | Not rated | 65-80% | 85% | |
| 12 | Not rated | 80-90% | 85% | |
| 13 | <75% | 90% | 90% | |
| 14 | 75-85% | 90% | 90% | |
| 15 Miller® FilTek XL | 85-95% | 90% | 90% | |
| Percentage of Weld Fume Particle Size ³ | 75-95% | 15% | 10% | |


¹American Society of Heating, Refrigeration and Air Conditioning Engineers (ASHRAE) 52.2

| Filter Media Type | Weld Fume Capture Efficiency | Pressure Drop | Relative Cost | |
|---------------------|------------------------------|---------------|---------------|--|
| Cellulose | Very low | Low | \$ | |
| Cellulose blend | Low | Moderate | \$ | |
| Spunbond polyester | Moderate/high | High | \$\$\$ | |
| Meltblown composite | High | High | \$\$ | |
| Miller FilTek XL | High | Low | \$\$ | |


FilTek XL filters provide high efficiencies and low operating pressure to out-filter, outperform, and outlast all the rest.

Not just filters — FilTek XL filters

The FilTek XL filter media design results in extended filter life, higher efficiency and stronger suction, resulting in a cleaner work space and improved weld fume capture. Filter media from FilTek XL high-volume filters are made up of a durable substrate with an engineered fiber designed to capture even the smallest of weld fume particles, while maintaining the highest level of efficiency.



Clean FilTek XL media



Surface loaded FilTek XL media (substrate still clean)



²National Air Filtration Association (NAFA) Guide

³Jenkins, Pierce, Edgar, Particle Size Distribution of GMAW and FCAW


Telescoping Extraction Arm

Pre-assembled arms for easy setup.



Easy-to-use telescoping arm is ideal for small spaces and offers reliable and accurate positioning across the full range of motion of the arm. Easy adjustments and maintenance ensures long-lasting operation. Pre-assembled telescoping arms can extend from 3 to 4.5 feet.

Durable bellmouth-shaped hood features a convenient 360 degree rotation for unlimited positioning. The FILTAIR extraction hood captures weld fumes at a greater distance from the source than other hood designs. This also means less hood adjustments for longer welds.






Standard Extraction Arm



Easy-to-operate standard arm with external adjustments so air can pass through with less airflow resistance, giving you stronger CFM (airflow). It offers reliable and accurate positioning across the full range of motion of the arm, as well as easy adjustment and maintenance to ensure long-lasting operation. Pre-assembled extraction arms are available in 7-, 10- or 12-foot lengths.

Durable belimouth-shaped hood features a convenient 360 degree rotation for unlimited positioning. The FILTAIR extraction hood captures weld fumes at a greater distance from the source than other hood designs. This also means less hood adjustments for longer welds.






ZoneFlow™ **Extraction Arm**



Easy-to-operate ZoneFlow arm with external adjustments so air can pass through with less airflow resistance, giving you stronger cfm (airflow). It offers reliable and accurate positioning across the full range of motion of the arm, as well as easy adjustment and maintenance to ensure long-lasting operation. Extraction arms are available in 10- or 12-foot lengths.

ZoneFlow arm creates a negative pressure zone that funnels air to the center of the arm from greater distances. The arm features convenient 360-degree rotation for unlimited positioning, which means fewer hood adjustments and extended welding time.






ZoneFlow™ Set-Up Guide

1. The fume extraction zone

ZoneFlow technology is designed to create a large, effective weld fume extraction zone. It will operate most effectively in areas where air currents or turbulence are minimal. When used properly, it will capture a large percentage of the fumes at the source, and the larger capture area will allow a welder to complete more welding while reducing interaction with the arm.



Air discharge clear area

To maximize the fume extraction zone, DO NOT OBSTRUCT AIR DISCHARGE from the arm.



The arm discharges clean, filtered air just behind the hood at approximately a 90-degree angle, creating an "air curtain" that funnels the weld fumes towards the center of the arm, maximizing capture. Maintain at least a 5-foot clear area ON ALL SIDES of the hood to avoid disturbing this air discharge. Disrupting the flow will reduce the amount and distance of fume captured.

2. Hood position and operator safety


ZoneFlow technology is designed to help protect the user from welding-specific airborne contaminants but must be used correctly to be fully effective.

Position the hood in front of or at side of the weld area in order to draw weld fumes AWAY from the operator. To maximize the extraction zone the angle of arm should be 30–45 degrees off horizontal.

DO NOT position the hood behind the welder, or in any other place that will cause the weld fumes to be pulled across the welder or through his breathing space.

BE AWARE that air turbulence or movement may disrupt the effectiveness or position of the fume extraction zone and increase the possibility that the welder may encounter weld fumes.

KEEP HEAD OUT OF FUMES!






ZoneFlow[™] **Set-Up Guide**


3. The effects of air currents or turbulence

ZoneFlow technology is designed to operate most effectively in areas where air currents or turbulence are minimal.




4. Compensate for air currents using screens or curtains

For the most efficient fume extraction in some environments, it may be necessary to actively manage the air currents to establish more predictable and stationary air space.





Workstations and Training Booths





Packages

Telescoping arm

Telescoping arm packages include:

- SWX filter cabinet (choose disposable filter or self-cleaning model)
- · High-efficiency filter
- 115 V cleaning control box (self-cleaning model only)
- 115 V blower
- 115 V on/off control box
- · Mounting bracket for blower/arm
- Flexible duct (7 x 37 in.)
- 8 in. diameter telescoping arm (3-4.5 ft.)

Note: 115 V wiring not included.

Telescoping dual-arm add-on package includes:

- 115 V blower
- 115 V on/off control box
- · Mounting bracket for blower/arm
- Flexible duct (7 x 37 in.)
- · Backdraft dampers
- 8 in. diameter telescoping arm (3-4.5 ft.)

Note: 115 V wiring not included.



Standard/ZoneFlow™ arm

Standard/ZoneFlow arm packages include:


- SWX filter cabinet (Standard: disposable filter or self-cleaning) (ZoneFlow: self-cleaning)
- · High-efficiency filter
- 115 V cleaning control box (self-cleaning model only)
- ZoneFlow motor control box (ZoneFlow packages only)
- 115 V blower
- 115 V on/off control box
- · Mounting bracket for blower/arm
- Flexible duct (7 x 37 in.)
- 8 in. diameter arm (Standard: 7, 10 or 12 ft.) (ZoneFlow: 10 or 12 ft.)

Note: 115 V wiring not included.

Standard/ZoneFlow dual-arm add-on packages include:

- 115 V blower
- 115 V on/off control box
- ZoneFlow motor control box (ZoneFlow packages only)
- Mounting bracket for blower/arm
- Flexible duct (7 x 37 in.)
- · Backdraft dampers
- 8 in. diameter arm (Standard: 7, 10 or 12 ft.) (ZoneFlow: 10 or 12 ft.)

Note: 115 V wiring not included.





Genuine Miller® Accessories



FilTek® XL Replacement Filters 300539 Disposable 300540 Self-cleaning (shown)



SWX Hood Light with Arc Sensor 300763 Field The hood light with arc sensor illuminates the welding zone and enables the fume extractor to start automatically when welding begins.

Note: Not compatible with ZoneFlow extraction arms.

Ordering Information

| EIL TAID® CMV D (Dienoschie Eilter) Cingle Arm Deckeges | 951619 | | | |
|--|------------------|---|---|--|
| FILTAIR® SWX-D (Disposable Filter) Single-Arm Packages (Includes SWX-D cabinet, disposable filter, blower, on/off control box, mounting bracket, duct, and | | With 3-4.5 ft. telescoping extraction arm | | |
| | | With 7 ft. standard extraction arm | | |
| B in. diameter arm. 115 V wiring NOT included.) | 951514 951515 | With 10 ft. standard extraction arm With 12 ft. standard extraction arm | | |
| FILTAIR® SWX-S (Self-Cleaning Filter) Single-Arm Packages | 951620 | With 3-4.5 ft. telescoping extraction arm | | |
| (Includes SWX-S cabinet, self-cleaning control box | 951516 | With 7 ft. standard extraction arm | | |
| and filter, blower, on/off control box, mounting bracket, | 951517 | With 10 ft. standard extraction arm | | |
| duct, and 8 in. diameter arm. 115 V wiring NOT included.) | 951518 | With 12 ft. standard extraction arm | | |
| | 951760 951761 | With 10 ft. ZoneFlow™ extraction arm and motor control box With 12 ft. ZoneFlow™ extraction arm and motor control box | | |
| FILTAID® ONLY Duel Asses Add On Declares | | | + | |
| FILTAIR® SWX Dual-Arm Add-On Packages (Includes blower, on/off control box, mounting bracket, | 951621 951519 | With 3 – 4.5 ft. telescoping extraction arm With 7 ft. standard extraction arm | | |
| duct, backdraft dampers, and 8 in. diameter arm. | 951519 | With 10 ft. standard extraction arm | | |
| 115 V wiring NOT included.) | 951521 | With 12 ft. standard extraction arm | | |
| | 951762 | With 10 ft. ZoneFlow™ extraction arm and motor control box | | |
| | 951822 | With 12 ft. ZoneFlow™ extraction arm and motor control box | | |
| Base Components | | | | |
| SWX Cabinet | 300599 | With disposable filter | | |
| (Includes filter and duct) | 300600 | With self-cleaning control box and filter | | |
| FEB-1 Fume Extraction Blower (Includes on/off control box and mounting bracket) | 300691 | 1 horsepower (FEB-1) | | |
| Telescoping Extraction Arm (Arm only) | 301237 | 3-4.5 ft. length, 8 in. diameter | | |
| Standard Extraction Arms (Arm only) | 300980 | SA-W807, 7 ft. length, 8 in. diameter | | |
| | 300981 300982 | SA-W810, 10 ft. length, 8 in. diameter | | |
| ZoneFlow™ Extraction Arms and ZoneFlow Motor Control Box | 951758 | SA-W812, 12 ft. length, 8 in. diameter SA-W810-ZF, 10 ft. length, 8 in. diameter | | |
| ZONEFIOW EXTRACTION ATMS and ZONEFIOW MOTOR CONTROL BOX | 951756 | SA-W810-ZF, 10 it. length, 8 in. diameter SA-W812-ZF, 12 ft. length, 8 in. diameter | | |
| FilTek® XL Replacement Filters | | | | |
| Disposable Filter | 300539 | | | |
| Self-Cleaning Filter | 300540 | | | |
| Accessories | | | | |
| SWX Hood Light with Arc Sensor | 300763 | Field. Not compatible with ZoneFlow extraction arms | | |

Date: Total Quoted Price:

Please call toll-free 855-FILTAIR (855-345-8247) for information on fume extraction solutions.

Distributed by:

